

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Servizi di distribuzione di energia



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICAZIONI



CARATTERISTICHE

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICHE

Table 1/2

Numero catalogo	Rack Height	Profondità	Usable Width	Montaggio	È conforme a	EMC Shielding
20860-621	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-622	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-624	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-625	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-626	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-627	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-628	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-629	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-630	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-632	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-633	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-634	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-635	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Numero catalogo	Product Family	Product Type	Tipo	Certificazioni
20860-621	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-622	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-624	MultipacPRO	Subrack/Chassis	Perforato	

Numero catalogo	Product Family	Product Type	Tipo	Certificazioni
20860-625	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-626	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-627	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-628	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-629	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-630	MultipacPRO	Subrack/Chassis	Perforato	
20860-632	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-633	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-634	MultipacPRO	Subrack/Chassis	Perforato	RoHS
20860-635	MultipacPRO	Subrack/Chassis	Perforato	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE