

RackPower Basic PDU, RB0xxx, 230 VAC, 1-phase

Servizi di distribuzione di energia

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

CARATTERISTICHE

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Input connector IEC 60309 332P6

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFICHE

Table 1/2

Numero catalogo	Product Type	Socket Type	Colore	Lunghezza	Voltage AC	Profondità
RB0328	Socket Strip	IEC C13, IEC C19	Nero	1490 mm	230 V	53 mm

Table 2/2

Numero catalogo	Larghezza
RB0328	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE