

Varistar CP Double Glazed Door, IP 20, 3-Point Locking

Servizi di distribuzione di energia

CARATTERISTICHE

Lever handle with key insert (2 keys)

Frame, St, 1.5 mm

Opening angle 180°

Security glass, 6 mm

Can be retrofitted with DIN profile half cylinder

Ingress protection class IP 20

Standard fitting, lock on right-hand door

SPECIFICHE

Table 1/2

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	Locking Type
21630-686	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-687	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-688	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-689	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-690	33 U	1600 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-691	33 U	1600 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	Locking Type
21630-692	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-693	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-694	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-695	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-696	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-697	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Numero catalogo	Product Type	Protection Rating	Tipo
21630-686	Cabinet Door	IP20	Glass Double Door
21630-687	Cabinet Door	IP20	Glass Double Door
21630-688	Cabinet Door	IP20	Glass Double Door
21630-689	Cabinet Door	IP20	Glass Double Door
21630-690	Cabinet Door	IP20	Glass Double Door
21630-691	Cabinet Door	IP20	Glass Double Door
21630-692	Cabinet Door	IP20	Glass Double Door
21630-693	Cabinet Door	IP20	Glass Double Door
21630-694	Cabinet Door	IP20	Glass Double Door
21630-695	Cabinet Door	IP20	Glass Double Door
21630-696	Cabinet Door	IP20	Glass Double Door

Numero catalogo	Product Type	Protection Rating	Tipo
21630-697	Cabinet Door	IP20	Glass Double Door

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE