


E650C-G Ground Sensor for Elexant 650c-Modbus



Ground sensor for combined measurement of temperature and moisture values in outdoor areas with foot or vehicle traffic. Robust version made of brass, fully encapsulated. Very low installation height, so particularly well suited to staircases, terraces, etc.

CARATTERISTICHE

Cable connection: To the side

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

SPECIFICHE

Table 1/2

Numero catalogo	Nome articolo	Comunicazione	Diametro	Hazardous Area	Altezza	Classe di protezione IP
1244-022796	E650C-G-HOUSING	No	68 mm	No	31 mm	IP68
1244-022794	E650C-G	No	68 mm	No	72 mm	IP68

Table 2/2

Numero catalogo	Nome articolo	Measuring Range
1244-022796	E650C-G-HOUSING	
1244-022794	E650C-G	-20 to 30 °C

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT