

ETL Self-Regulating Heating Cable



nVent RAYCHEM ETL self-regulating trace heating cables provide energy efficient pipe freeze protection. R-ETL-A/B are suitable for on- or in-pipe applications, R-ETL(-A/B)-CR for on-pipe only. Each are available in two power outputs (10 and 16 W/m at 5 °C), supported by a full range of heat shrinkable connections and accessories.

CARATTERISTICHE

Simple to design, with fluoropolymer jacket option for use in pipes

Easy to install: small geometry, cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICHE

Nominal Thickness:	5,8 mm
Nominal Width:	8,5 mm
Min Bending Radius:	10 mm
Max Continuous Exposure Temperature, Power Off:	65 °C
Supply Voltage:	220 - 240 V
Temperatura minima di installazione:	-20 °C
Colore:	Nero
Ground Path Type:	e collegamento
Materiale conduttore:	Nickel-Plated Copper

Table 1/1

Numero catalogo	Nome articolo	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Max Circuit Length, In-Pipe
924269-000	R-ETL-A	16 W/m	10 W/m	100 m	60 m
P000002042	R-ETL-B	25 W/m	16 W/m	100 m	60 m

Numero catalogo	Nome articolo	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max CircuitLength	Max Circuit Length, In-Pipe
P000002043	R-ETL-A-CR		10 W/m	100 m	
P000002044	R-ETL-B-CR		16 W/m	100 m	

ADDITIONAL PRODUCT DETAILS

Maximum circuit lengths are based on 230 VAC supply and C-Type characteristic circuit protection devices, switch-on at 5 °C.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT