

FrostGuard Self-Regulating Cable Kit



nVent RAYCHEM FrostGuard kits contain self regulating trace heating cables, pre-installed with electrical cable and plug to provide an energy-efficient and easy-to-use solution for pipe freeze protection.

CARATTERISTICHE

Simple to design: kit format, available in 17 sizes

Easy to install: small and flexible trace heating cable, pre-installed with a plug and cold lead to avoid the need for connection by an electrician, ideal for small diameter pipework and condensate pipework of condensing boilers

Energy efficient and safe: self-regulating cable, no overheating possible even when overlapped or closely spaced

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICHE

Cold Lead Length:	2 m
Nominal Height:	5,8 mm
Nominal Width:	8,5 mm
Nominal Power Output @ 5°C, 230V:	10 W/m
Max Continuous Exposure Temperature, Power Off:	65 °C
Tensione nominale:	230 V
Temperatura minima di installazione:	-5 °C
Colore:	Nero
Ground Path Type:	e collegamento
Outer Jacket Material:	Fluoropolimero
Heating Cable Technology:	Self-Regulating

Table 1/1

Numero catalogo	Nome articolo	Nominal Power Output, In-Pipe @ 230V	Lunghezza
1244-022826	FROSTGUARD-30M	16 W/m	30 m

Numero catalogo	Nome articolo	Nominal Power Output, In-Pipe @ 230V	Lunghezza
1244-022827	FROSTGUARD-35M	16 W/m	35 m
1244-022828	FROSTGUARD-40M	16 W/m	40 m
1244-022829	FROSTGUARD-50M	16 W/m	50 m
1244-022830	FROSTGUARD-60M	16 W/m	60 m
1244-022831	FROSTGUARD-80M		80 m
1244-022832	FROSTGUARD-100M		100 m
107442-000	FROSTGUARD-22M	16 W/m	22 m
108722-000	FROSTGUARD-13M	16 W/m	13 m
468683-000	FROSTGUARD-19M	16 W/m	19 m
493074-000	FROSTGUARD-8M	16 W/m	8 m
524628-000	FROSTGUARD-4M	16 W/m	4 m
641438-000	FROSTGUARD-10M	16 W/m	10 m
768868-000	FROSTGUARD-25M	16 W/m	25 m
845612-000	FROSTGUARD-6M	16 W/m	6 m
924248-000	FROSTGUARD-16M	16 W/m	16 m
928206-000	FROSTGUARD-2M	16 W/m	2 m

ADDITIONAL PRODUCT DETAILS

Subject to local norms and approvals, FrostGuard can be used for in-pipe applications. For in-pipe applications (where permitted) install using a nVent RAYCHEM approved pipe entry gland assembly.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT