

GREEN LEAF Programmable Thermostat



nVent RAYCHEM GREEN LEAF is a modern design 'wall flush mounted' programmable thermostat for electrical floor heating. It can work in floor or room sensing mode or in room sensing mode with floor temperature limiter. Eco Design compliant thanks to the following functions: Room temperature control, with open window detection. For more details, please consult the Commissioning sheet (INST324 or EU2550). RAYCHEM GREEN LEAF is a modern design 'wall flush mounted' programmable thermostat for electrical floor heating. It can work in floor or room sensing mode or in room sensing mode with floor temperature limiter. Eco Design compliant thanks to the following functions: Room temperature control, with open window detection. For more details, please consult the Commissioning sheet (INST324 or EU2550).

CARATTERISTICHE

Easy to set up and operate: smart 'leaf button'; simple timer event programming with possibility to group days

Flexible control: editable pre-set program; 7 day with 4 timer events; different temperatures possible for each timer event; timer or constant temperature function

Optimum heat management, with 2 sensors: ambient and floor sensor

Reliable during long life: 12 to 20 year total care warranty available, maintenance free

SPECIFICHE

Table 1/4

Numero catalogo	Nome articolo	Power Supply	Adjustable Differential	Regulation Type	Max Contact Load	Max Contact Voltage
1244-017312	R-GREEN-LEAF-EU	230 V	No	On/Off	13 A	230 V

Table 2/4

Numero catalogo	Nome articolo	Current Rating	Sensor/Feeler Type	Remote Operation	Power Consumption, Standby	Classe di protezione IP
1244-017312	R-GREEN-LEAF-EU	13 A	Resistance Sensor	No	3 W	IP21

Table 3/4

Numero catalogo	Nome articolo	RAL Number	IFTTT Support Available	Clock Type	Clock Model	Self Learning
1244-017312	R-GREEN-LEAF-EU	9005	No	Day Clock	Digitale	Sì.

Table 4/4

Numero catalogo	Nome articolo	Altezza	Larghezza	Profondità
1244-017312	R-GREEN-LEAF-EU	86.3 mm	86.3 mm	41 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT