

Integrated Junction Box for Direct Connection of PI cables



nVent RAYCHEM JBx-PI-E(P) junction boxes are used for direct connection of XPI(-S) heating cables to a power supply, without the need of a cold lead, or for splicing. They come with an integrated pipe stand, an earth plate and external earth stud. There are 3 variations: two (2) are used for power connection (JBS-PI-EP, JBM-PI-EP); one (1) is used for splicing (JB-SPLICE-PI-E). They support monophase and triphase configurations, up to 45A operational current (depending on heating cable and temperature), and the design is integrated in TraceCalc Pro. Suitable for use in hazardous area.

CARATTERISTICHE

Simplified BOM (no cold lead, no support bracket, no insulation entry kit)

Simplified & faster installation (no hot-cold connections / no special tools / connection with cage clamp terminals)

Hazardous area approved

Different versions (supporting multiple configurations)

Design validated through nVent design software TraceCalc Pro

SPECIFICHE

For Ex-Zone Gas:	1, 2
Max Conductor Cross Section:	16 mm ²
For Ex-Zone Dust:	21, 22
Tipo di connessione:	Cold Applied
Materiale:	Glass Fiber Reinforced Polymer
Area Classification:	Non-Hazardous; Hazardous
Classe di protezione IP:	IP66
Knockouts Included:	No
Below Insulation:	No
Montaggio:	On Pipe
Cover Attachment:	Screwed
Non contiene alogeni:	Sì.
Ambient Temperature:	da -55 a 56 °C

Table 1/2

Numero catalogo	Nome articolo	Inlet Quantity	Cable Entry	Connection Clamp Quantity	Altezza	Larghezza
P000004430	JB-SPLICE-PI-E	0	N.A.	5	160 mm	260 mm
P000004429	JBM-PI-EP	1	M32	5	120 mm	220 mm
P000004428	JBS-PI-EP	1	M25	3	120 mm	122 mm

Table 2/2

Numero catalogo	Nome articolo	Profondità	Earth Plate Included
P000004430	JB-SPLICE-PI-E	90 mm	No
P000004429	JBM-PI-EP	90 mm	Sì.
P000004428	JBS-PI-EP	90 mm	Sì.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT