

MONI-PT100-4/20MA Sensor Assembly for Hazardous Areas



nVent RAYCHEM MONI-PT100-4/20MA is a PT100 sensor connected to a 4-20 mA transmitter built into a black glass fiber reinforced polyester junction box. Suitable for hazardous areas.

CARATTERISTICHE

Simple and fast to install: built in a black glass fiber reinforced polyester junction box with blue M20 cable gland

Temperature measuring range: -50 °C to +250 °C

SPECIFICHE

Table 1/2

Numero catalogo	Nome articolo	Housing Material	Montaggio	Max Measuring Range	Temperatura di esercizio	Fixed Cable to Sensor
704058-000	PT100-4/20MA	Glass Fibre Reinforced Polyester	Bracket	250 °C	-20 to 55 °C	Sì.

Table 2/2

Numero catalogo	Nome articolo	Lunghezza del cavo	Sensor Tip Diameter
704058-000	PT100-4/20MA	2 m	3 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT