

NGC-40 Series, Power Distribution and Supply Panel

nVent RAYCHEM NGC-40 Panel Solution is a multipoint electronic control, monitoring and power distribution system with a unique single-point controller architecture, providing the most reliable central control and monitoring solution for your heat management system. Supporting up to 32 circuits per panel, the system offers fully flexible configuration and individual single-phase and three-phase controllers with SIL2 safety temperature limiters. System status and faults are reported to the user, displayed on the nVent RAYCHEM Touch 1500 user interface or remotely using nVent RAYCHEM Supervisor software.

CARATTERISTICHE

Easy to install, configure and operate

Extensive control, monitoring, alarm and power distribution capabilities

Modular, providing configuration and component flexibility: optimizing project specific needs and costs

Comprehensive communications, system status and faults are reported with messages and alarms: optimizing maintenance and recovery time

SPECIFICHE

Main Switch Current Rating: 160 A

Voltage Rating: 240 V

Table 1/1

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014353	PSS-160A/10KA-PDS-40-12HTC/25A-2HTC3/40A	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	No
1244-014352	PSS-160A/10kA-PDS-40-12HTC/25A-2HTC3/40A-T	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	Si.

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014348	PSS-160A/10KA-PDS-40-24HTC/16A-T	24	16 A, Type C	24 x NGC-40-HTC	Sì.
1244-014350	PSS-160A/10KA-PDS-40-30HTC/16A-T	30	16 A, Type C	30 x NGC-40-HTC	Sì.
1244-014351	PSS-160A/10KA-PDS-40-30HTC/16A	30	16 A, Type C	30 x NGC-40-HTC	No
1244-014349	PSS-160A/10KA-PDS-40-24HTC/16A	24	16 A, Type C	24 x NGC-40-HTC	No

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT