

NGC-40 Series, Power Termination Module



nVent RAYCHEM NGC-40 Series - Power Termination Module accepts a primary and redundant power supply input, also accepts CAN bus inputs and provides for termination of the CAN bus. Each NGC-40-PTM can provide power for a maximum of 10 NGC-40 modules.

CARATTERISTICHE

Din-rail mounted and part of the NGC-40 system

Provides primary power and CAN bus inputs/termination to the NGC-40 system

Easy to install and reliable

SPECIFICHE

Table 1/2

Codice a catalogo	Nome articolo	Tensione nominale	Tipo di tensione nominale	Corrente nominale a 24 V CC	Temperatura di esercizio	Altezza
10730-005	NGC-40-PTM	24 V	CC	1.5 A	-40 to 65 °C	87 mm

Table 2/2

Codice a catalogo	Nome articolo	Larghezza	Profondità
10730-005	NGC-40-PTM	45 mm	106.4 mm

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Il nostro straordinario portafoglio di marchi:

RAYCHEM PYROTENAX TRACER NUHEAT