

SBS Control Panel for Hot Water Temperature Maintenance



nVent RAYCHEM SBS-XX-HX-ECO-10 control panel provides an integrated solution for nVent RAYCHEM self-regulating heating cables in single pipe hot water temperature maintenance applications. It includes the energy efficient HWAT-ECO control system and offers multi-circuit, multi-sensor and multi-control with integrated electrical protection. A 400 VAC (3 phase) supply is required.

CARATTERISTICHE

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 1-9 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: with HWAT-ECO control system integrated (providing standard, economy, and 'tap time' set-back timer functions)

System monitoring, with alarm functions, including monitoring of boiler output temperature and low temperature alarm

Reliable, a complete system from one manufacturer, specifically designed for single pipe hot water temperature maintenance applications

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICHE

Classe di protezione IP: IP65

Montaggio: Wall Mounted

Table 1/2

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Altezza
035958-000	SBS-03-HV-ECO-10	3	20 A, Type C	32 A	1	600 mm

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Altezza
539268-000	SBS-06-HV-ECO-10	6	20 A, Type C	63 A	2	600 mm
294452-000	SBS-09-HV-ECO-10	9	20 A, Type C	63 A	3	600 mm

Table 2/2

Numero catalogo	Nome articolo	Larghezza	Profondità
035958-000	SBS-03-HV-ECO-10	400 mm	210 mm
539268-000	SBS-06-HV-ECO-10	600 mm	210 mm
294452-000	SBS-09-HV-ECO-10	600 mm	210 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT