

SBS Control Panel for Surface Snow Melting



nVent RAYCHEM SBS-XX-VV-20 control panels provides an integrated solution for nVent RAYCHEM self-regulating heating cables in surface snow melting applications. It offers multi-circuit, multi-sensor and multi-control with integrated electrical protection. Driven by the built-in smart nVent RAYCHEM VIA-DU-20 control device, it allows the system only to be activated when cold weather and moisture are detected in combination. A 400 VAC (3 phase) supply is required.

CARATTERISTICHE

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 3-12 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: through built-in VIA-DU-20 smart controller, circuits energized only when cold weather and moisture are detected

Reliable, complete system from one manufacturer and specifically designed for surface snow melting systems

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICHE

Classe di protezione IP: IP65

Housing Material: Acciaio

Montaggio: Wall Mounted

Table 1/2

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Altezza	Larghezza
1244-000219	SBS-03-MV-20	3	32 A	0	600 mm	400 mm
1244-000220	SBS-06-MV-20	6	63 A	0	600 mm	600 mm
1244-000221	SBS-09-MV-20	9	63 A	0	800 mm	800 mm

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Altezza	Larghezza
1244-000222	SBS-12-MV-20	12	63 A	0	800 mm	800 mm
1244-000223	SBS-15-MV-20	15	100 A	0	800 mm	800 mm
1244-000224	SBS-18-MV-20	18	125 A	0	1000 mm	800 mm
1244-000215	SBS-03-VV-20	3	63 A	1	600 mm	400 mm
1244-006430	SBS-03-CM-20	3	32 A	1	600 mm	400 mm
1244-006434	SBS-03-CW-40	3	32 A	1	600 mm	400 mm
1244-000216	SBS-06-VV-20	6	100 A	2	600 mm	600 mm
1244-006431	SBS-06-CM-20	6	63 A	2	600 mm	600 mm
1244-006435	SBS-06-CW-40	6	100 A	2	600 mm	600 mm
1244-000217	SBS-09-VV-20	9	100 A	3	800 mm	800 mm
1244-000218	SBS-12-VV-20	12	160 A	4	800 mm	800 mm
1244-006432	SBS-09-CM-20	9	63 A	3	600 mm	600 mm
1244-006433	SBS-12-CM-20	12	100 A	4	800 mm	800 mm
1244-006436	SBS-09-CW-40	9	100 A	3	800 mm	800 mm
1244-006437	SBS-12-CW-40	12	160 A	4	800 mm	800 mm
1244-006438	SBS-15-CW-40	15	160 A	5	1000 mm	800 mm
1244-006439	SBS-18-CW-40	18	250 A	6	1000 mm	800 mm
1244-008212	SBS-15-CM-20	15	125 A	5	800 mm	800 mm

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Altezza	Larghezza
1244-008213	SBS-18-CM-20	18	125 A	6	1000 mm	800 mm

Table 2/2

Numero catalogo	Nome articolo	Profondità
1244-000219	SBS-03-MV-20	210 mm
1244-000220	SBS-06-MV-20	210 mm
1244-000221	SBS-09-MV-20	210 mm
1244-000222	SBS-12-MV-20	210 mm
1244-000223	SBS-15-MV-20	210 mm
1244-000224	SBS-18-MV-20	210 mm
1244-000215	SBS-03-VV-20	210 mm
1244-006430	SBS-03-CM-20	210 mm
1244-006434	SBS-03-CW-40	210 mm
1244-000216	SBS-06-VV-20	210 mm
1244-006431	SBS-06-CM-20	210 mm
1244-006435	SBS-06-CW-40	210 mm
1244-000217	SBS-09-VV-20	210 mm
1244-000218	SBS-12-VV-20	210 mm
1244-006432	SBS-09-CM-20	210 mm
1244-006433	SBS-12-CM-20	210 mm

Numero catalogo	Nome articolo	Profondità
1244-006436	SBS-09-CW-40	210 mm
1244-006437	SBS-12-CW-40	210 mm
1244-006438	SBS-15-CW-40	300 mm
1244-006439	SBS-18-CW-40	300 mm
1244-008212	SBS-15-CM-20	210 mm
1244-008213	SBS-18-CM-20	300 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT