

SBS-XX-EV Control Panel for Roof and Gutter De-Icing

nVent RAYCHEM SBS-XX-EV-10 control panel provides an integrated solution for nVent RAYCHEM self-regulating heating cables in roof and gutter de-icing applications. It offers multi-circuits, multi-sensor, and multi-control with integrated electrical protection. Driven by the built-in smart nVent RAYCHEM EMDR-10 control device, it allows the system only to be activated when cold weather and moisture are detected in combination. A 400 VAC (3 phase) supply is required.

CARATTERISTICHE

Simple and fast connection of multiple circuits, directly into a single panel

High capacity, with 3-12 maximum circuit lengths connected into the panel

Fully integrated system: all connections, circuit protection and safety devices integrated into the panel

Energy saving: through built-in EMDR-10 smart controller, circuits energized only when cold weather and moisture are detected

Reliable, complete system from one manufacturer and specifically designed for roof and gutter de-icing systems

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICHE

Classe di protezione IP: IP65

Housing Material: Acciaio

Montaggio: Wall Mounted

Table 1/2

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30 mA	Altezza
295014-000	SBS-03-EV-10	3	20 A, Type C	32 A	1	600 mm
458484-000	SBS-06-EV-10	6	20 A, Type C	63 A	2	600 mm
282458-000	SBS-12-EV-10	12	20 A, Type C	100 A	4	800 mm

Numero catalogo	Nome articolo	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating	Circuit Breaker Quantity, 30mA	Altezza
206336-000	SBS-09-EV-10	9	20 A, Type C	63 A	3	600 mm

Table 2/2

Numero catalogo	Nome articolo	Larghezza	Profondità
295014-000	SBS-03-EV-10	400 mm	210 mm
458484-000	SBS-06-EV-10	600 mm	210 mm
282458-000	SBS-12-EV-10	800 mm	210 mm
206336-000	SBS-09-EV-10	600 mm	210 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT