

T2Blue Floor Heating Cable



nVent RAYCHEM T2Blue is an electrical floor heating cable for new build projects where the cable is installed directly in 10-15 mm of screed (T2Blue-10) or in 30-50 mm of screed (T2Blue-20). The cable does exist in 2 power output variants of 10 W/m and 20W/m and available in pre-terminated lengths (11-200 m). The range is composed of installer friendly kits including the cable on a spool and all installation accessories. Variants without thermostat and including the SENZ WIFI touchscreen thermostat are available.

CARATTERISTICHE

Easy installation: flexible cable, pre-terminated with power cable

T2Blue-10 is typically installed in low construction floors (10-15 mm), directly in screed, in self levelling compound or in uncoupling membrane

T2Blue-20 is typically installed in high construction floors (30-50 mm), directly in screed on concrete sub-floors or on insulation boards

Safe and efficient operation: flexible power output from 60 to 150W/m², closer loops for higher output and wider loops for lower output

Installer friendly kits with easy to unroll spooling system and all installation accessories included

Available in kits without thermostat and in EcoDesign compatible kits including the energy efficient and advanced SENZ WIFI touchscreen thermostat that can be controlled through the SENZ WIFI app or through voice control using Alexa or Google Assistant compatible smart speakers.

Reliable during long life: 12 to 20 year total care warranty available, no maintenance required

SPECIFICHE

Cold Lead Length:	2,5 m
Temperatura minima di installazione:	5 °C
Diametro esterno:	5,5 mm
Min Cable Spacing:	50 mm
Tensione nominale:	230 V
Colore:	Blu
Ground Path Type:	e collegamento
Heating Cable Technology:	Constant Wattage
Outer Jacket Material:	Low Smoke Zero Halogen
Spooling System:	Sì.

Table 1/2

Numero catalogo	Nome articolo	Nominal Power Output	Potenza	Power Output, Typical	Resistance Range	Lunghezza
SZ18300401	R-BL-A-25M/SENZ-WIFI	10 W/m	250 W	60 – 125 W/m ²	201.9 – 233.8 Ω	25 m
SZ18300402	R-BL-A-30M/SENZ-WIFI	10 W/m	305 W	60 – 125 W/m ²	165.3 – 191.4 Ω	30 m
SZ18300403	R-BL-A-40M/SENZ-WIFI	10 W/m	400 W	60 – 125 W/m ²	125.4 – 145.2 Ω	40 m
SZ18300404	R-BL-A-50M/SENZ-WIFI	10 W/m	505 W	60 – 125 W/m ²	99.8 – 115.5 Ω	50 m
SZ18300405	R-BL-A-60M/SENZ-WIFI	10 W/m	605 W	60 – 125 W/m ²	83.2 – 96.4 Ω	60 m
SZ18300406	R-BL-A-70M/SENZ-WIFI	10 W/m	700 W	60 – 125 W/m ²	71.8 – 83.2 Ω	70 m
SZ18300407	R-BL-A-80M/SENZ-WIFI	10 W/m	805 W	60 – 125 W/m ²	62.3 – 72.2 Ω	80 m
SZ18300408	R-BL-A-90M/SENZ-WIFI	10 W/m	890 W	60 – 125 W/m ²	56.4 – 65.3 Ω	90 m
SZ18300409	R-BL-A-101M/SENZ-WIFI	10 W/m	1010 W	60 – 125 W/m ²	49.9 – 57.8 Ω	101 m
SZ18300410	R-BL-A-121M/SENZ-WIFI	10 W/m	1215 W	60 – 125 W/m ²	41.4 – 47.9 Ω	121 m
SZ18300411	R-BL-A-142M/SENZ-WIFI	10 W/m	1420 W	60 – 125 W/m ²	35.1 – 40.6 Ω	142 m
SZ18300412	R-BL-A-160M/SENZ-WIFI	10 W/m	1600 W	60 – 125 W/m ²	30.4 – 35.2 Ω	160 m
SZ18300413	R-BL-A-180M/SENZ-WIFI	10 W/m	1800 W	60 – 125 W/m ²	27.4 – 31.7 Ω	180 m
SZ18300414	R-BL-A-200M/SENZ-WIFI	10 W/m	2000 W	60 – 125 W/m ²	24.7 – 28.6 Ω	200 m
SZ18300415	R-BL-C-11M/SENZ-WIFI	20 W/m	205 W	80 – 150 W/m ²	246.6 – 285.6 Ω	11 m
SZ18300416	R-BL-C-14M/SENZ-WIFI	20 W/m	285 W	80 – 150 W/m ²	176.9 – 204.8 Ω	14 m

Numero catalogo	Nome articolo	Nominal Power Output	Potenza	Power Output, Typical	Resistance Range	Lunghezza
SZ18300417	R-BL-C-18M/SENZ-WIFI	20 W/m	355 W	80 – 150 W/m ²	145.4 – 168.3 Ω	18 m
SZ18300418	R-BL-C-21M/SENZ-WIFI	20 W/m	435 W	80 – 150 W/m ²	115.7 – 134 Ω	21 m
SZ18300419	R-BL-C-28M/SENZ-WIFI	20 W/m	575 W	80 – 150 W/m ²	87.8 – 101.6 Ω	28 m
SZ18300420	R-BL-C-35M/SENZ-WIFI	20 W/m	720 W	80 – 150 W/m ²	69.8 – 80.9 Ω	35 m
SZ18300421	R-BL-C-43M/SENZ-WIFI	20 W/m	845 W	80 – 150 W/m ²	59.6 – 69.1 Ω	43 m
SZ18300422	R-BL-C-50M/SENZ-WIFI	20 W/m	980 W	80 – 150 W/m ²	51.3 – 59.4 Ω	50 m
SZ18300423	R-BL-C-57M/SENZ-WIFI	20 W/m	1130 W	80 – 150 W/m ²	44.4 – 51.4 Ω	57 m
SZ18300424	R-BL-C-63M/SENZ-WIFI	20 W/m	1270 W	80 – 150 W/m ²	39.5 – 45.7 Ω	63 m
SZ18300425	R-BL-C-71M/SENZ-WIFI	20 W/m	1435 W	80 – 150 W/m ²	35.1 – 40.6 Ω	71 m
SZ18300426	R-BL-C-86M/SENZ-WIFI	20 W/m	1710 W	80 – 150 W/m ²	29.4 – 34.1 Ω	86 m
SZ18300427	R-BL-C-101M/SENZ-WIFI	20 W/m	2015 W	80 – 150 W/m ²	24.9 – 28.9 Ω	101 m
SZ18300428	R-BL-C-115M/SENZ-WIFI	20 W/m	2300 W	80 – 150 W/m ²	21.9 – 25.3 Ω	115 m
1244-001887	R-BL-A-101M/T0/SD	10 W/m	1010 W	60 – 125 W/m ²	49.9 – 57.8 Ω	101 m
1244-001902	R-BL-C-101M/T0/SD	20 W/m	2015 W	80 – 150 W/m ²	24.9 – 28.9 Ω	101 m
SZ18300369	R-BL-A-10M/T0/SD	10 W/m	100 W	60 – 125 W/m ²	503.5 – 583 Ω	10 m
SZ18300370	R-BL-A-15M/T0/SD	10 W/m	150 W	60 – 125 W/m ²	336.3 – 389.4 Ω	15 m
SZ18300371	R-BL-A-20M/T0/SD	10 W/m	200 W	60 – 125 W/m ²	252.7 – 292.6 Ω	20 m
SZ18300372	R-BL-A-25M/T0/SD	10 W/m	250 W	60 – 125 W/m ²	201.9 – 233.8 Ω	25 m

Numero catalogo	Nome articolo	Nominal Power Output	Potenza	Power Output, Typical	Resistance Range	Lunghezza
SZ18300373	R-BL-A-30M/T0/SD	10 W/m	305 W	60 – 125 W/m ²	165.3 – 191.4 Ω	30 m
SZ18300374	R-BL-A-40M/T0/SD	10 W/m	400 W	60 – 125 W/m ²	125.4 – 145.2 Ω	40 m
SZ18300375	R-BL-A-50M/T0/SD	10 W/m	505 W	60 – 125 W/m ²	99.8 – 115.5 Ω	50 m
SZ18300376	R-BL-A-60M/T0/SD	10 W/m	605 W	60 – 125 W/m ²	83.2 – 96.4 Ω	60 m
SZ18300377	R-BL-A-70M/T0/SD	10 W/m	700 W	60 – 125 W/m ²	71.8 – 83.2 Ω	70 m
SZ18300378	R-BL-A-80M/T0/SD	10 W/m	805 W	60 – 125 W/m ²	62.3 – 72.2 Ω	80 m
SZ18300379	R-BL-A-90M/T0/SD	10 W/m	890 W	60 – 125 W/m ²	56.4 – 65.3 Ω	90 m
SZ18300380	R-BL-A-121M/T0/SD	10 W/m	1215 W	60 – 125 W/m ²	41.4 – 47.9 Ω	121 m
SZ18300381	R-BL-A-142M/T0/SD	10 W/m	1420 W	60 – 125 W/m ²	35.1 – 40.6 Ω	142 m
SZ18300382	R-BL-A-160M/T0/SD	10 W/m	1600 W	60 – 125 W/m ²	30.4 – 35.2 Ω	160 m
SZ18300383	R-BL-A-180M/T0/SD	10 W/m	1800 W	60 – 125 W/m ²	27.4 – 31.7 Ω	180 m
SZ18300384	R-BL-A-200M/T0/SD	10 W/m	2000 W	60 – 125 W/m ²	24.7 – 28.6 Ω	200 m
SZ18300385	R-BL-C-11M/T0/SD	20 W/m	205 W	80 – 150 W/m ²	246.6 – 285.6 Ω	11 m
SZ18300386	R-BL-C-14M/T0/SD	20 W/m	285 W	80 – 150 W/m ²	176.9 – 204.8 Ω	14 m
SZ18300387	R-BL-C-18M/T0/SD	20 W/m	355 W	80 – 150 W/m ²	145.4 – 168.3 Ω	18 m
SZ18300388	R-BL-C-21M/T0/SD	20 W/m	435 W	80 – 150 W/m ²	115.7 – 134 Ω	21 m
SZ18300389	R-BL-C-28M/T0/SD	20 W/m	575 W	80 – 150 W/m ²	87.8 – 101.6 Ω	28 m
SZ18300390	R-BL-C-35M/T0/SD	20 W/m	720 W	80 – 150 W/m ²	69.8 – 80.9 Ω	35 m

Numero catalogo	Nome articolo	Nominal Power Output	Potenza	Power Output, Typical	Resistance Range	Lunghezza
SZ18300391	R-BL-C-43M/T0/SD	20 W/m	845 W	80 – 150 W/m ²	59.6 – 69.1 Ω	43 m
SZ18300392	R-BL-C-50M/T0/SD	20 W/m	980 W	80 – 150 W/m ²	51.3 – 59.4 Ω	50 m
SZ18300393	R-BL-C-57M/T0/SD	20 W/m	1130 W	80 – 150 W/m ²	44.4 – 51.4 Ω	57 m
SZ18300394	R-BL-C-63M/T0/SD	20 W/m	1270 W	80 – 150 W/m ²	39.5 – 45.7 Ω	63 m
SZ18300395	R-BL-C-71M/T0/SD	20 W/m	1435 W	80 – 150 W/m ²	35.1 – 40.6 Ω	71 m
SZ18300396	R-BL-C-86M/T0/SD	20 W/m	1710 W	80 – 150 W/m ²	29.4 – 34.1 Ω	86 m
SZ18300397	R-BL-C-115M/T0/SD	20 W/m	2300 W	80 – 150 W/m ²	21.9 – 25.3 Ω	115 m
SZ18300398	R-BL-A-10M/SENZ-WIFI	10 W/m	100 W	60 – 125 W/m ²	503.5 – 583 Ω	10 m
SZ18300399	R-BL-A-15M/SENZ-WIFI	10 W/m	150 W	60 – 125 W/m ²	336.3 – 389.4 Ω	15 m
SZ18300400	R-BL-A-20M/SENZ-WIFI	10 W/m	200 W	60 – 125 W/m ²	252.7 – 292.6 Ω	20 m

Table 2/2

Numero catalogo	Nome articolo	Thermostat Included
SZ18300401	R-BL-A-25M/SENZ-WIFI	SENZ-WIFI
SZ18300402	R-BL-A-30M/SENZ-WIFI	SENZ-WIFI
SZ18300403	R-BL-A-40M/SENZ-WIFI	SENZ-WIFI
SZ18300404	R-BL-A-50M/SENZ-WIFI	SENZ-WIFI
SZ18300405	R-BL-A-60M/SENZ-WIFI	SENZ-WIFI
SZ18300406	R-BL-A-70M/SENZ-WIFI	SENZ-WIFI
SZ18300407	R-BL-A-80M/SENZ-WIFI	SENZ-WIFI

Numero catalogo	Nome articolo	Thermostat Included
SZ18300408	R-BL-A-90M/SENZ-WIFI	SENZ-WIFI
SZ18300409	R-BL-A-101M/SENZ-WIFI	SENZ-WIFI
SZ18300410	R-BL-A-121M/SENZ-WIFI	SENZ-WIFI
SZ18300411	R-BL-A-142M/SENZ-WIFI	SENZ-WIFI
SZ18300412	R-BL-A-160M/SENZ-WIFI	SENZ-WIFI
SZ18300413	R-BL-A-180M/SENZ-WIFI	SENZ-WIFI
SZ18300414	R-BL-A-200M/SENZ-WIFI	SENZ-WIFI
SZ18300415	R-BL-C-11M/SENZ-WIFI	SENZ-WIFI
SZ18300416	R-BL-C-14M/SENZ-WIFI	SENZ-WIFI
SZ18300417	R-BL-C-18M/SENZ-WIFI	SENZ-WIFI
SZ18300418	R-BL-C-21M/SENZ-WIFI	SENZ-WIFI
SZ18300419	R-BL-C-28M/SENZ-WIFI	SENZ-WIFI
SZ18300420	R-BL-C-35M/SENZ-WIFI	SENZ-WIFI
SZ18300421	R-BL-C-43M/SENZ-WIFI	SENZ-WIFI
SZ18300422	R-BL-C-50M/SENZ-WIFI	SENZ-WIFI
SZ18300423	R-BL-C-57M/SENZ-WIFI	SENZ-WIFI
SZ18300424	R-BL-C-63M/SENZ-WIFI	SENZ-WIFI
SZ18300425	R-BL-C-71M/SENZ-WIFI	SENZ-WIFI

Numero catalogo	Nome articolo	Thermostat Included
SZ18300426	R-BL-C-86M/SENZ-WIFI	SENZ-WIFI
SZ18300427	R-BL-C-101M/SENZ-WIFI	SENZ-WIFI
SZ18300428	R-BL-C-115M/SENZ-WIFI	SENZ-WIFI
1244-001887	R-BL-A-101M/T0/SD	No
1244-001902	R-BL-C-101M/T0/SD	No
SZ18300369	R-BL-A-10M/T0/SD	No
SZ18300370	R-BL-A-15M/T0/SD	No
SZ18300371	R-BL-A-20M/T0/SD	No
SZ18300372	R-BL-A-25M/T0/SD	No
SZ18300373	R-BL-A-30M/T0/SD	No
SZ18300374	R-BL-A-40M/T0/SD	No
SZ18300375	R-BL-A-50M/T0/SD	No
SZ18300376	R-BL-A-60M/T0/SD	No
SZ18300377	R-BL-A-70M/T0/SD	No
SZ18300378	R-BL-A-80M/T0/SD	No
SZ18300379	R-BL-A-90M/T0/SD	No
SZ18300380	R-BL-A-121M/T0/SD	No
SZ18300381	R-BL-A-142M/T0/SD	No

Numero catalogo	Nome articolo	Thermostat Included
SZ18300382	R-BL-A-160M/T0/SD	No
SZ18300383	R-BL-A-180M/T0/SD	No
SZ18300384	R-BL-A-200M/T0/SD	No
SZ18300385	R-BL-C-11M/T0/SD	No
SZ18300386	R-BL-C-14M/T0/SD	No
SZ18300387	R-BL-C-18M/T0/SD	No
SZ18300388	R-BL-C-21M/T0/SD	No
SZ18300389	R-BL-C-28M/T0/SD	No
SZ18300390	R-BL-C-35M/T0/SD	No
SZ18300391	R-BL-C-43M/T0/SD	No
SZ18300392	R-BL-C-50M/T0/SD	No
SZ18300393	R-BL-C-57M/T0/SD	No
SZ18300394	R-BL-C-63M/T0/SD	No
SZ18300395	R-BL-C-71M/T0/SD	No
SZ18300396	R-BL-C-86M/T0/SD	No
SZ18300397	R-BL-C-115M/T0/SD	No
SZ18300398	R-BL-A-10M/SENZ-WIFI	SENZ-WIFI
SZ18300399	R-BL-A-15M/SENZ-WIFI	SENZ-WIFI

Numero catalogo	Nome articolo	Thermostat Included
SZ18300400	R-BL-A-20M/SENZ-WIFI	SENZ-WIFI

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT