

TT5000-HUV Fuel Sensing Cable for Aboveground Piping, Modular



nVent RAYCHEM TraceTek TT5000-HUV is a hydrocarbon sensing cable for use on aboveground pipe, around pump pads or valves where the cable will be exposed to sunlight and weather during its service life. The cable is designed to be attached to the bottom of horizontal piping, spiraled around vertical pipe, or placed on flat surfaces below or around pumps and valves and other applications where surface level fuel leaks and spills can be anticipated. Installed with an alarm and locating module, the cable ignores water and detects hydrocarbon fuel leaks, triggers an alarm and pinpoints the location.

CARATTERISTICHE

Advanced technology: radiation crosslinking and conductive polymer technology, mechanically strong and resistant to chemicals

Simple and fast to install

Easy to design: available in fixed modular lengths, or in bulk form for cut-to-length in field, or in custom cut lengths with connectors attached in the factory

Well documented response times: standard nVent RAYCHEM TraceTek TT5000 sensing core

Distinctive appearance: black rope with red stripe, ready for refinery, tank farm and terminal applications

Flexible and rugged: rope outer layer is fabricated with thousands of individual filaments that add strength and UV protection

Reliable during long life: 5 year product warranty available, maintenance free

SPECIFICHE

Diametro esterno:	10,2 mm
Max Operating Temperature:	60 °C
Detection:	Carburante
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
P000001299	TT5000-HUV-15M-MC	15 m

Numero catalogo	Nome articolo	Lunghezza
P000001302	TT5000-HUV-1M-MC	1 m
P000001296	TT5000-HUV-100M-MC	100 m
P000001300	TT5000-HUV-7.5M-MC	7.5 m
P000001298	TT5000-HUV-30M-MC	30 m
P000001301	TT5000-HUV-3M-MC	3 m
P000001297	TT5000-HUV-50M-MC	50 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT