

Varistar CP EMC Perforated Steel Door, Seismic, Multi-Point Locking, glazed steel, 1800H 800W

CODICE A CATALOGO

21630-771



EMC doors with good contact with the frame and gasket to achieve high attenuation.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

CARATTERISTICHE

Perforated door with Multi-Point locking for Seismic & EMC applications

Opening angle 180°

Lever handle with push button

ATTRIBUTI DEL PRODOTTO

Quantità nella confezione: 1

Finitura: Verniciato a polvere

Materiale: Acciaio

Tipo di prodotto: Sportello dell'armadio

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Please purchase the grounding kit separately.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE