

Guida orizzontale, anteriore, tipo R-KD, robusta, labbro corto, 40 CV

CODICE A CATALOGO

34566-240



Combinations of horizontal rails and side panels

		3" x 6" can be combined	3" x 6" combination not recommended	network kit required
Network 10		-	-	+
Network 12		network kit required for 3" x 6" combination	network kit required and side panel must be installed	+
Network 14		network kit required	network kit required	-
Decorative rail		-	-	+
Side panel	   	1000 x 1	Decorative 1"	Network 12 or Network 14






La robusta guida orizzontale è in grado di gestire urti e vibrazioni fino a 25 g.

CERTIFICAZIONI



CARATTERISTICHE

Guida orizzontale "robusta" di tipo R-KD con fissaggio a 3 fori per una maggiore robustezza

Alluminio estruso, finitura anodizzata, superficie di contatto conduttiva, con contrassegni HP

ATTRIBUTI DEL PRODOTTO

Larghezza rack: 40HP

Quantità imballaggio: 1

Fine: Anodizzato

Lunghezza: 208.28mm

Materiale: Alluminio

Famiglia di prodotti: EuropacPRO

Tipo di prodotto: Guida orizzontale

Tipo: Robusto, KD

Funziona con: Subracks

Gross Weight: 0.118kg

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Senza filettatura M4 sul lato anteriore, senza stampa e senza tacca per staffa da 19".

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE