

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 42 HP

CODICE A CATALOGO

34566-242



Combinations of horizontal rails and side panels

+ = can be combined, - = combination not recommended

Heavy 1.8		-	-	-	side rail is required
Heavy 1.2		-	side rail is needed for the front panel	side rail is needed for the front panel	+
Light 1.2		+	side rail is needed for the front panel	side rail is needed for the front panel	+
Light 1.0		side rail is required	side rail is needed	-	-
Decorative rail		-	-	-	-
Side panel					
	Light 1.2	Decorative	Heavy 1.2	Heavy 1.8	Support 1.8

Light 1.2 Decorative Heavy 1.2 Heavy 1.8 Support 1.8

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICAZIONI



CARATTERISTICHE

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

ATTRIBUTI DEL PRODOTTO

Larghezza rack: 42HP

Quantità nella confezione: 1

Finitura: Anodizzato

Lunghezza: 218.44mm

Materiale: Alluminio

Famiglia di prodotti: EuropacPRO

Tipo di prodotto: Guida orizzontale

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Without M4 thread to front, without printing and without notch for 19" bracket.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE