

E225 Card-Lok

CODICE A CATALOGO

VE225-3.80T2



The Series E225 Card Lok features an integrated ejector, actuated by the screw, the force disengages the PC card from its mating connector without damaging circuits, components or connector pins.

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CERTIFICAZIONI



CARATTERISTICHE

Profile 5.72 mm (0.225") x 6.86 mm (0.270")

For cold wall applications

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

3 segment, non-shafted design

Weight 1.34 g/cm (0.120 oz/')

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Flexible mounting options

Min expansion 8.26 mm (0.325")

Screw actuated

Integrated ejector

Average clamp force (4.80", black anodized) = 274 lbs

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Fermo PCB

Materiale: Alluminio

Tipo: Senza albero

Prestazioni termiche: Medio

Profilo: 5.72 x 6.86 mm

Forza di serraggio: 91 – 136kgf

Larghezza di separazione: PCB + (7.0 - 7.9 mm)

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE