

EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

Subrack with reinforced horizontal rails and side panels for backplane mounting.



CERTIFICAZIONI



CARATTERISTICHE

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

Horizontal rail type "rugged"

SPECIFICHE

Materiale:	Alluminio
Finitura:	Anodizzato; Passivato
Tipo di prodotto:	Rack secondario/Telaio
Schermatura EMC:	Sì

Table 1/3

Codice a catalogo	Altezza del rack	Profondità	Quantità nella confezione	Per il montaggio	Profondità scheda	Tipo di guarnizione EMC
24567-149	3U	295mm	1	Backplane	160mm	Tessuto
24567-449	6U	295mm	1	Backplane	160mm	Tessuto

Table 2/3

Codice a catalogo	Tolleranza agli urti e alle vibrazioni	Maniglia in dotazione	Montaggio	È conforme a	Larghezza rack	Carico statico
24567-149	25g (force)	Sì	Rack	CODICE 60297-3-103, IEEE 1101,10, IEEE 1101,11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	84HP	25kg
24567-449	25g (force)	Sì	Rack	CODICE 60297-3-103, IEEE 1101,10, IEEE 1101,11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	84HP	25kg

Table 3/3

Codice a catalogo	Spedizione rapida
24567-149	No
24567-449	No

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE