

# 3x Temperature and 1x Humidity Sensor

## Data Solutions

### CODICE A CATALOGO

**EA9105**



3x Temperature and 1x Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

### CARATTERISTICHE

3x Temperature and 1x Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

Second and Third Temperature Sensor with 950 mm cable

### ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sensore

Funziona con: RackPower

Altezza: 270mm

Quantità nella confezione: 1

Tipo di spina: RJ45

Famiglia di prodotti: Enlogic

Cavo di ingresso rimovibile: No

## AVVERTIMENTO

---

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**