

CS480 Straight Coupling



CS480 Straight Coupling attaches a tube to the enclosure, enabling 340-degree enclosure rotation. Maintenance-free bearings.

STANDARD INDUSTRIAL

IEC 60529, IP66

CARATTERISTICHE

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICHE

Table 1/1						
Codice a catalogo	Altezza	Larghezza	Profondità	Materiale	Finitura	Spedizione rapida
CCSS48FC	60mm	84mm	84mm	Acciaio inossidabile 304	Spazzolato	No

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE