

Telaio per rack oscillante per impieghi gravosi



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

CARATTERISTICHE

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

SPECIFICHE

Spessore: 2.66mm
Colore: Grigio chiaro
Fine: Verniciato a polvere
Codice colore: RAL 7035

Table 1/1

Codice a catalogo	Materiale	Adatta alla larghezza del telaio	Unità rack	Spedizione rapida
PSF76	Acciaio dolce	600mm	10U	No
PSF146	Acciaio dolce	600mm	25U	No
PSF148	Acciaio dolce	800mm	25U	No
PSF78	Acciaio dolce	800mm	10U	No
PSF168	Acciaio dolce	800mm	30U	No
PSF186	Acciaio dolce	600mm	34U	No
PSF188	Acciaio dolce	800mm	34U	No
PSF206	Acciaio dolce	600mm	39U	No
PSF77	Acciaio dolce	700mm	10U	No
PSF207	Acciaio dolce	700mm	39U	No
PSF208	Acciaio dolce	800mm	39U	No
PSF226	Acciaio dolce	600mm	43U	No
PSF227	Acciaio dolce	700mm	43U	No
PSF228	Acciaio dolce	800mm	43U	No
PSF166	Acciaio dolce	600mm	30U	No

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE