

ProLine Heavy-Duty Swing-Out Rack Frame



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

CARATTERISTICHE

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

SPECIFICHE

Table 1/1

| Codice a catalogo | Materiale | Colore | Codice colore | Finitura | Spessore | Spedizione rapida |
|-------------------|-------------------|---------------|---------------|----------------------|----------|-------------------|
| PSF187 | Lamiera d'acciaio | Grigio chiaro | RAL 7035 | Verniciato a polvere | 2.66mm | No |

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE