

19" Fan Unit, 1 U, Speed Control and Monitoring

Servizi di distribuzione di energia

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICAZIONI



CARATTERISTICHE

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFICHE

Table 1/1

Numero catalogo	Input Voltage AC	Input Voltage DC	Certificazioni
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Numero catalogo	Input Voltage AC	Input Voltage DC	Certificazioni
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE