

19" Pusher Fan, 3 U, Axial

Power Utilities

Fan tray with integrated pusher fan.



CERTIFICAZIONI



CARATTERISTICHE

Ventilation directed accurately to the electronics

19" Pusher Fan, 3 U, Axial

Air infeed from front, air exits at the top rear of cabinet (guided upwards by cover plates or via hoses to rear and upwards)

Contact protection in accordance with DIN EN ISO 13857

SPECIFICHE

Table 1/1

Codice a catalogo	Tensione di ingresso CA
10713-546	230 V min
10713-547	115 V min

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

With cover plates, this pusher fan can be re-fitted to different cooling concepts

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE