

RackPower Single Temperature and Humidity Sensor

Power Utilities

CODICE A CATALOGO

EA9103

Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

CARATTERISTICHE

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy $\pm 2\%$

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy $\pm 5\%$

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sensore

Tipo: Temperatura e umidità

Funziona con: RackPower

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle

istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE