


EuropacPRO 19" Subrack Kit for Backplane, Shielded

Servizi di distribuzione di energia

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



CERTIFICAZIONI



CARATTERISTICHE

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPECIFICHE

Product Type: Subrack/Chassis

Table 1/2						
Numero catalogo	Rack Height	Profondità	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/2						
Numero catalogo	Handle Included	Montaggio	È conforme a	EMC Shielding	Rack Width	Carico statico
24563-142	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-143	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-144	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-145	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf

Numero catalogo	HandleIncluded	Montaggio	È conforme a	EMC Shielding	Rack Width	Carico statico
24563-146	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-442	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-443	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-444	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-445	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf
24563-446	No	Rack	IEC 60297-3-103	Si.	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE