

Front Panel, Anodized With Untreated Edges, Unshielded

Servizi di distribuzione di energia

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



CERTIFICAZIONI



CARATTERISTICHE

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaggio	Front Finish
30818-271	2 U	84 HP	1	Nessuno	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Nessuno	Screw-on Front	Anodized

Numero catalogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaggio	Front Finish
30818-331	3 U	63 HP	1	Nessuno	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Nessuno	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Nessuno	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Nessuno	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Nessuno	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Nessuno	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Nessuno	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Nessuno	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Nessuno	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Nessuno	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Nessuno	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Nessuno	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Nessuno	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Nessuno	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Nessuno	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Nessuno	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Nessuno	Screw-on Front	Anodized
30818-284	3 U	16 HP		Nessuno	Screw-on Front	Anodized

Numero catalogo	Rack Height	Rack Width	Package Quantity	Handle Type	Montaggio	Front Finish
30818-289	3 U	21 HP	5	Nessuno	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Nessuno	Screw-on Front	Anodized
30818-517	6 U	3 HP		Nessuno	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Nessuno	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Nessuno	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Nessuno	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Nessuno	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Nessuno	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Nessuno	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Nessuno	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Nessuno	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Nessuno	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Nessuno	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Nessuno	Screw-on Front	Anodized

Table 2/3

Numero catalogo	Rear Finish	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale
30818-271	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Alluminio
30818-310	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio

Numero catalogo	Rear Finish	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale
30818-331	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-352	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-434	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Alluminio
30818-556	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-577	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-598	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30810-433	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-747	Anodized	Sì.	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-272	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-273	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-274	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-275	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-276	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-277	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio

Numero catalogo	Rear Finish	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale
30818-279	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-281	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-282	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-284	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-289	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-296	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Alluminio
30818-517	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-518	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-519	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-520	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-521	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-522	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-524	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-526	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio

Numero catalogo	Rear Finish	Treated Edges	È conforme a	EMC Shielding	Altezza	Materiale
30818-528	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-530	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-535	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio
30818-542	Anodized	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Alluminio

Table 3/3

Numero catalogo	Product Type	Tipo	Larghezza	Certificazioni
30818-271	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-310	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-331	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-352	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-434	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-556	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-577	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-598	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30810-433	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-747	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-272	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30818-273	Front Panel	Front Panel without Handle	20 mm	RoHS

Numero catalogo	Product Type	Tipo	Larghezza	Certificazioni
30818-274	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-275	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-276	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-277	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-279	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-281	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30818-282	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-284	Front Panel	Front Panel without Handle	80.9 mm	
30818-289	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-296	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30818-517	Front Panel	Front Panel without Handle	14.9 mm	
30818-518	Front Panel	Front Panel without Handle	20 mm	RoHS
30818-519	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-520	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-521	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-522	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-524	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-526	Front Panel	Front Panel without Handle	60.6 mm	RoHS

Numero catalogo	Product Type	Tipo	Larghezza	Certificazioni
30818-528	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-530	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30818-535	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-542	Front Panel	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE