

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket

Servizi di distribuzione di energia

Front panel, flat, with slot for stainless steel EMC gasket.

CERTIFICAZIONI



CARATTERISTICHE

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

SPECIFICHE

Table 1/2

Numero catalogo	Rack Width	Package Quantity	Montaggio	Front Finish	Rear Finish	Treated Edges
30846-682	63 HP	1	Screw-on Front			
30846-681	42 HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Numero catalogo	Altezza	Materiale	Product Type	Rack Height	Tipo	Larghezza
30846-682	172.9 mm	Alluminio	Front Panel	4 U	Front Panel without Handle	319.7 mm
30846-681	172.9 mm	Alluminio	Front Panel	4 U	Front Panel without Handle	213 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE