

# Varistar CP EMC Cabinet, IP 20

## Servizi di distribuzione di energia

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

### CARATTERISTICHE

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 20

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

### SPECIFICHE

Table 1/3

| Numero catalogo | Frame Material | Frame Color | Frame Color Code | Cladding Material | Cladding Color | Cladding Color Code |
|-----------------|----------------|-------------|------------------|-------------------|----------------|---------------------|
| 10630-045       | Acciaio        | Black Grey  | RAL 7021         | Acciaio           | Black Grey     | RAL 7021            |

Table 2/3

| Numero catalogo | Rack Height | Altezza | Larghezza | Profondità | Carico statico | Protection Rating |
|-----------------|-------------|---------|-----------|------------|----------------|-------------------|
| 10630-045       | 42 U        | 2000 mm | 600 mm    | 800 mm     | 1600 kgf       | IP20              |

Table 3/3

| Numero catalogo | È conforme a |
|-----------------|--------------|
|-----------------|--------------|

## ADDITIONAL PRODUCT DETAILS

---

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

## AVVERTENZA

---

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**