

# Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

## Servizi di distribuzione di energia

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

### CARATTERISTICHE

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

### SPECIFICHE

Table 1/2

| Numero catalogo | Rack Height | Altezza | Larghezza | Colore     | Color Code | È conforme a             |
|-----------------|-------------|---------|-----------|------------|------------|--------------------------|
| 21630-876       | 33 U        | 1600 mm | 600 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-877       | 33 U        | 1600 mm | 800 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-878       | 38 U        | 1800 mm | 600 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-879       | 38 U        | 1800 mm | 800 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-880       | 42 U        | 2000 mm | 600 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-881       | 42 U        | 2000 mm | 800 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |
| 21630-882       | 47 U        | 2200 mm | 600 mm    | Black Grey | RAL 7021   | IEC 61587-1, IEC 61587-2 |

| Numero catalogo | Rack Height | Altezza | Larghezza | Colore     | Color Code | È conforme a                |
|-----------------|-------------|---------|-----------|------------|------------|-----------------------------|
| 21630-883       | 47 U        | 2200 mm | 800 mm    | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

Table 2/2

| Numero catalogo | Locking Type    | Materiale | Product Type | Protection Rating | Tipo                   | Works With  |
|-----------------|-----------------|-----------|--------------|-------------------|------------------------|-------------|
| 21630-876       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-877       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-878       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-879       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-880       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-881       | 4-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-882       | 5-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-883       | 5-Point Locking | Acciaio   | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**