

Varistar CP Steel Door, Perforated With 3-Point Electronic Locking

Servizi di distribuzione di energia

Varistar CP perforated steel door 3-point locking for IP 20 applications.

CARATTERISTICHE

Perforated steel door with 3-point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICHE

Table 1/3

Numero catalogo	Rack Height	Altezza	Larghezza	Tipo	Colore	Color Code
21630-814	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-815	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-816	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-817	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-818	47 U	2200 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-819	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-895	42 U	2000 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-896	47 U	2200 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021

Numero catalogo	Rack Height	Altezza	Larghezza	Tipo	Colore	Color Code
21630-897	52 U	2450 mm	600 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-898	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-899	42 U	2000 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021
21630-900	52 U	2450 mm	800 mm	Steel Door, Perforated	Black Grey	RAL 7021

Table 2/3						
Numero catalogo	È conforme a	Finitura	Locking Type	Materiale	Product Type	Protection Rating
21630-814	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-815	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-816	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-817	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-818	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-819	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-895	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-896	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-897	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-898	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-899	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20
21630-900	IEC 61587-1	Verniciato a polvere	3-Point Locking, Electronic	Acciaio	Cabinet Door	IP20

Table 3/3

Numero catalogo	Works With
21630-814	Varistar CP
21630-815	Varistar CP
21630-816	Varistar CP
21630-817	Varistar CP
21630-818	Varistar CP
21630-819	Varistar CP
21630-895	Varistar CP
21630-896	Varistar CP
21630-897	Varistar CP
21630-898	Varistar CP
21630-899	Varistar CP
21630-900	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE