

Varistar CP Steel Door, Perforated With 3-Point Locking

Servizi di distribuzione di energia

Varistar CP perforated steel door 3-point locking for IP 20 applications.

CARATTERISTICHE

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICHE

Table 1/2

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	È conforme a
21630-098	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-099	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-100	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-101	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-102	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-103	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-424	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	È conforme a
21630-425	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-426	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-427	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-428	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-429	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-430	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-431	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Numero catalogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-098	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-099	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-100	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-101	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-102	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-103	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-424	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-425	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-426	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-427	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

Numero catalogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-428	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-429	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-430	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-431	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE