

# Varistar CP Steel Door, Perforated With Multi-Point Locking

## Servizi di distribuzione di energia

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

### CARATTERISTICHE

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

### SPECIFICHE

Table 1/2

| Numero catalogo | Rack Height | Altezza | Larghezza | Colore     | Color Code | Locking Type    |
|-----------------|-------------|---------|-----------|------------|------------|-----------------|
| 21630-533       | 24 U        | 1200 mm | 600 mm    | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-534       | 24 U        | 1200 mm | 800 mm    | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-535       | 29 U        | 1400 mm | 600 mm    | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-536       | 29 U        | 1400 mm | 800 mm    | Black Grey | RAL 7021   | 3-Point Locking |
| 21630-537       | 33 U        | 1600 mm | 600 mm    | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-538       | 33 U        | 1600 mm | 800 mm    | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-539       | 38 U        | 1800 mm | 600 mm    | Black Grey | RAL 7021   | 4-Point Locking |

| Numero catalogo | Rack Height | Altezza | Larghezza | Colore     | Color Code | Locking Type    |
|-----------------|-------------|---------|-----------|------------|------------|-----------------|
| 21630-540       | 38 U        | 1800 mm | 800 mm    | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-541       | 42 U        | 2000 mm | 600 mm    | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-542       | 42 U        | 2000 mm | 800 mm    | Black Grey | RAL 7021   | 4-Point Locking |
| 21630-543       | 47 U        | 2200 mm | 600 mm    | Black Grey | RAL 7021   | 5-Point Locking |
| 21630-544       | 47 U        | 2200 mm | 800 mm    | Black Grey | RAL 7021   | 5-Point Locking |

Table 2/2

| Numero catalogo | Materiale | Product Type | Tipo                   |
|-----------------|-----------|--------------|------------------------|
| 21630-533       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-534       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-535       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-536       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-537       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-538       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-539       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-540       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-541       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-542       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-543       | Acciaio   | Cabinet Door | Steel Door, Perforated |
| 21630-544       | Acciaio   | Cabinet Door | Steel Door, Perforated |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## AVVERTENZA

---

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**