

Varistar CP Steel Door, Plain With 3-Point Locking and Brush Strip, Shortened

Servizi di distribuzione di energia

Shortened door available for IP20, IP55 applications.

CARATTERISTICHE

Height of connection plate 400 mm

Connection plate with brush strip

The height of the door is 400 mm less than the cabinet height

SPECIFICHE

Table 1/2

Numero catalogo	Rack Height	Altezza	Larghezza	Colore	Color Code	Locking Type
21630-348	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-349	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-350	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-351	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-352	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-353	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Numero catalogo	Product Type	Protection Rating
-----------------	--------------	-------------------

21630-348	Cabinet Door	IP20
21630-349	Cabinet Door	IP20
21630-350	Cabinet Door	IP20
21630-351	Cabinet Door	IP20
21630-352	Cabinet Door	IP20
21630-353	Cabinet Door	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE