

Gland Metric



nVent PYROTENAX Gland Metric are a range of externally threaded metric brass glands (RGM).

CARATTERISTICHE

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICHE

Materiale: Metallo

Thread Type: Metrico

Table 1/1

Numero catalogo	Nominal Thread Size, Metric/PG	Pitch Thread	Diametro del cavo	Hex Dimension
RGM2L120	20	11 mm	5.1 mm	24 mm
RGM1H2.520	20	11 mm	5.3 mm	24 mm
RGM2L1.520	20	11 mm	5.7 mm	24 mm
RGM3L120	20	11 mm	5.8 mm	24 mm
RGM4L120	20	11 mm	6.3 mm	24 mm
RGM3L1.520	20	11 mm	6.4 mm	24 mm

Numero catalogo	Nominal Thread Size, Metric/PG	Pitch Thread	Diametro del cavo	Hex Dimension
RGM2L2.520	20	11 mm	6.6 mm	24 mm
RGM4L1.520	20	11 mm	7 mm	24 mm
RGM1H1020	40	11 mm	7.3 mm	24 mm
RGM1H1025	25	16 mm	7.3 mm	30 mm
RGM3L2.520	20	11 mm	7.3 mm	24 mm
RGM7L125	25	16 mm	7.6 mm	30 mm
RGM2L420	20	11 mm	7.7 mm	24 mm
RGM2H1.520	20	11 mm	7.9 mm	24 mm
RGM4L2.520	20	11 mm	8.1 mm	24 mm
RGM1H1620	20	11 mm	8.3 mm	24 mm
RGM1H1625	25	16 mm	8.3 mm	30 mm
RGM3H1.520	20	11 mm	8.3 mm	24 mm
RGM7L1.525	25	16 mm	8.4 mm	30 mm
RGM2H2.520	20	11 mm	8.7 mm	24 mm
RGM4H1.520	20	11 mm	9.1 mm	24 mm
RGM3H2.520	20	11 mm	9.3 mm	24 mm
RGM3H2.525	25	16 mm	9.3 mm	30 mm
RGM1H2520	20	11 mm	9.6 mm	24 mm

Numero catalogo	Nominal Thread Size, Metric/PG	Pitch Thread	Diametro del cavo	Hex Dimension
RGM1H2532	32	17.5 mm	9.6 mm	36 mm
RGM7L2.525	25	16 mm	9.7 mm	30 mm
RGM2H420	20	11 mm	9.8 mm	24 mm
RGM2H425	25	16 mm	9.8 mm	30 mm
RGM4H2.520	20	11 mm	10.1 mm	24 mm
RGM4H2.525	25	16 mm	10.1 mm	30 mm
RGM3H420	20	11 mm	10.4 mm	24 mm
RGM3H425	25	16 mm	10.4 mm	30 mm
RGM1H3520	20	11 mm	10.7 mm	24 mm
RGM1H3532	32	17.5 mm	10.7 mm	36 mm
RGM7H1.525	25	16 mm	10.8 mm	30 mm
RGM2H620	20	11 mm	10.9 mm	24 mm
RGM2H625	25	16 mm	10.9 mm	30 mm
RGM1H620	20	11 mm	13.7 mm	24 mm
RGM4H425	25	16 mm	11.4 mm	30 mm
RGM3H625	25	16 mm	11.5 mm	30 mm
RGM1H5025	25	16 mm	12.1 mm	30 mm
RGM1H5040	40	26 mm	12.1 mm	46 mm

Numero catalogo	Nominal Thread Size, Metric/PG	Pitch Thread	Diametro del cavo	Hex Dimension
RGM7H2.525	25	16 mm	12.1 mm	30 mm
RGM4H632	32	17.5 mm	12.7 mm	36 mm
RGM2H1025	25	16 mm	12.7 mm	30 mm
RGM2H1032	32	17.5 mm	12.7 mm	36 mm
RGM4H625	25	16 mm	12.7 mm	30 mm
RGM3H1025	25	16 mm	13.6 mm	30 mm
RGM3H1032	32	17.5 mm	13.6 mm	36 mm
RGM1H7025	25	16 mm	13.7 mm	30 mm
RGM12H1.532	32	17.5 mm	14.1 mm	36 mm
RGM2H1625	25	16 mm	14.7 mm	30 mm
RGM2H1640	40	26 mm	14.7 mm	46 mm
RGM4H1025	25	16 mm	14.8 mm	30 mm
RGM4H1032	32	17.5 mm	14.8 mm	36 mm
RGM12H2.532	32	17.5 mm	15.4 mm	36 mm
RGM1H9525	25	16 mm	15.4 mm	30 mm
RGM19H1.540	40	26 mm	15.6 mm	46 mm
RGM3H1625	25	16 mm	15.6 mm	30 mm
RGM3H1640	40	26 mm	15.6 mm	46 mm

Numero catalogo	Nominal Thread Size, Metric/PG	Pitch Thread	Diametro del cavo	Hex Dimension
RGM1H12032	32	17.5 mm	16.8 mm	36 mm
RGM1H15032	32	17.5 mm	18.4 mm	36 mm
RGM1H18532	32	17.5 mm	20.4 mm	36 mm
RGM1H24040	40	26 mm	23.3 mm	46 mm
RGM2H2532	32	17.5 mm	17.1 mm	36 mm
RGM2H2540	40	26 mm	17.1 mm	46 mm
RGM3H2540	40	26 mm	18.2 mm	46 mm
RGM4H1632	32	17.5 mm	17.3 mm	36 mm
RGM4H1640	40	26 mm	17.3 mm	46 mm
RGM4H2540	40	26 mm	20.1 mm	46 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT