


ACS-30 Sensing and Monitoring Module



The nVent RAYCHEM ACS-30-EU-ELEXANT650C-SMDI-MOD Module for the ACS-30 system provides smart sensor input for surface snow melting and roof & gutter de-icing applications. The Remote Monitoring Module (RMM) is used to collect sensor/temperature inputs for monitoring of the heat tracing circuits of an ACS-30 control system.

CARATTERISTICHE

The output from the ACS-30-EU-ELEXANT650C-SMDI-MOD module enables the switching of the heating circuits within the power & control module (PCM)

The ACS-30-EU-ELEXANT650C-SMDI-MOD module provides ground or roof & gutter temperature and moisture sensing for the ACS-30 control system

Ground temperature and moisture sensor (E650C-G) and roof & gutter temperature and moisture sensor (E650C-R) are sold separately

The RMM provides up to 8 sensor inputs per module with feedback to the ACS-30-EU-UIT3 interface

A single twisted pair RS-485 cable connects up to 247 RMM units providing additional temperature monitoring sensor inputs

The RMM is remotely located adjacent to the desired measurement locations

The RMM comes in 2 versions: ACS-30-EU-RMM3 (230 V) and ACS-30-EU-RMM3-24VDC (24 V), both pre-installed inside a compact enclosure

SPECIFICHE

Table 1/2

Numero catalogo	Nome articolo	Profondità	Altezza	Housing Material	Classe di protezione IP	Montaggio
2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	132 mm	262 mm	Polycarbonato	IP20	Wall Mounted

Table 2/2

Numero catalogo	Nome articolo	Larghezza
-----------------	---------------	-----------

2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	332 mm
------------	--------------------------------	--------

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT