

ArcticStep Panel



nVent RAYCHEM ArcticStep is a modular panel heating system and consists of a robust metallic top plate, an embedded RAYCHEM self-regulating heating cable, fiber reinforced polymer supports, protective anti-slip coating and adjustable fixations.

CARATTERISTICHE

Simple and fast to install: a light-weight system, available in different sizes and power outputs, attached to the deck with adjustable fixations

Energy efficient: a self-regulating heating cable, with conductive compound and fiber reinforced polymer supports to ensure thermal insulation from the deck and exact amount of heat where it is most needed

Safe and reliable: through a bright yellow durable anti-slip coating, galvanic isolation from the deck and integrated power cable channels for protection against mechanical damage

Compliant with international offshore standards: DNV-GL approval

Reliable during long life, even in harsh corrosive environments: 10 year product warranty available, maintenance free

SPECIFICHE

Cold Lead Length: 10 m
Tensione nominale: 230 V
Area Classification: Non-Hazardous; Hazardous

Table 1/1

Numero catalogo	Minimum Power Output @ -20°C, 230V	Modular Panel Type	Lunghezza	Larghezza	Altezza
RAS-500-C-1.0-10	500 W/m ²	Corner	1000 mm	1000 mm	35 mm
RAS-500-S-1.0-10	500 W/m ²	Dritto	1000 mm	1000 mm	35 mm
RAS-350-S-1.0-10	350 W/m ²	Dritto	1000 mm	1000 mm	35 mm
RAS-500-S-2.0-10	500 W/m ²	Straight Long	2000 mm	1000 mm	35 mm

Numero catalogo	Minimum Power Output @ -20°C, 230V	Modular Panel Type	Lunghezza	Larghezza	Altezza
RAS-650-C-1.0-10	650 W/m ²	Corner	1000 mm	1000 mm	35 mm
RAS-650-S-1.0-10	650 W/m ²	Dritto	1000 mm	1000 mm	35 mm
RAS-350-C-1.0-10	350 W/m ²	Corner	1000 mm	1000 mm	35 mm
RAS-650-S-2.0-10	650 W/m ²	Straight Long	2000 mm	1000 mm	35 mm
RAS-350-S-2.0-10	350 W/m ²	Straight Long	2000 mm	1000 mm	35 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT