

Connection Kit for PI Heaters Into Junction Box

nVent RAYCHEM C20-PI-M0 and C20-PI-PA are a range of kits to connect polymer insulated (PI) heaters into a junction box. The C20-PI-M0-KIT contains cable gland Ex e (M20), nickel-plated brass, for use with XPI cold leads up to -55 °C. The C20-PI-PA-KIT contains cable gland Ex e (M20), polyamide, for use with XPI cold leads up to -40 °C. All kits include green/yellow sleeves for braid and locknut.

CARATTERISTICHE

Hazardous area approved

Simple and fast to install, easy to maintain

Reliable during long life: 10 year product warranty available

SPECIFICHE

Thread Type: Metrico

Table 1/1

Numero catalogo	Nome articolo	Materiale	Finitura	Ambient Temperature	Suitable for PI Cables with Diameter Range
1244-019669	C20-PI-PA-KIT	Poliammide	Untreated	-40 to 75 °C	4 – 13 mm
1244-019670	C20-PI-M0-KIT	Ottone	Nickel-Plated	-55 to 90 °C	5 – 14 mm

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT