

IceStop Self-Regulating Cable Kit



nVent RAYCHEM IceStop self-regulating trace heating cable kits provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

CARATTERISTICHE

Simple to design

Easy to install, pre-terminated kits: 5 - 30 m, each with 8 m power cable, GM-RAKE fixing bracket and RayClic end seal

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICHE

Nominal Height:	6 mm
Cold Lead Length:	8 m
Nominal Width:	14 mm
Nominal Power Output, In Air @ 0°C, 230V:	18 W/m
Nominal Power Output, In Ice Water @ 0°C, 230V:	36 W/m
Max Continuous Exposure Temperature, Power On:	65 °C
Max Intermittent Exposure Temperature, Power On:	85 °C
Nominal Cable Weight:	120 g/m
Supply Voltage:	220 - 240 V
Max Cumulative Hours for Intermittent Exposure:	800 h
Temperatura minima di installazione:	-18 °C
Colore:	Nero
Ground Path Type:	e collegamento
Outer Jacket Material:	Modified Polyolefin
Heating Cable Technology:	Self-Regulating

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
-----------------	---------------	-----------

106160-000	GM-2X-SA-8	8 m
159067-000	GM-2X-SA-12	12 m
191808-000	GM-2X-SA-5	5 m
650854-000	GM-2X-SA-16	16 m
838627-000	GM-2X-SA-25	25 m
925956-000	GM-2X-SA-30	30 m
973923-000	GM-2X-SA-20	20 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT