

TT1000 Water Sensing Cable, Modular



nVent RAYCHEM TraceTek TT1000-XX-PC are a range of fixed length water sensing cables with factory installed plastic connectors. Mainly used in commercial building applications, it is typically intended for leak detection under raised floors, in mechanical rooms and similar flat surface areas. It detects the presence of water at any point along its length. Installed with an alarm and locating module, the cable senses water leaks, triggers an alarm and pinpoints the location.

CARATTERISTICHE

Advanced technology: rugged conductive polymer and fluoropolymer construction, resistant to corrosion and abrasion

Simple and fast to install: small, lightweight and flexible

Easy to design, fast drying, and reuseable

Distributed leak detection and location over a wide range of areas

Reliable and durable, 10 year product warranty available

SPECIFICHE

Diametro esterno:	6 mm
Max Operating Temperature:	75 °C
Detection Method:	Raychem Conductive-Polymer Technology
Detection:	Water

Table 1/1

Numero catalogo	Nome articolo	Lunghezza
017859-000	TT1000-7.5M/25FT-PC	7.5 m
072827-000	TT1000-5M/17FT-PC	5 m
391887-000	TT1000-3M/10FT-PC	3 m
396807-000	TT1000-30M/100FT-PC	30 m

Numero catalogo	Nome articolo	Lunghezza
409271-000	TT1000-1M/3FT-PC	1 m
805147-000	TT1000-15M/50FT-PC	15 m
P000000702	TT1000-100M/330FT-PC	100 m
P000000864	TT1000-25M/82FT-PC	25 m
P000000873	TT1000-50M/165FT-PC	50 m
P000001222	TT1000-6M/20FT-PC	6 m
P000001223	TT1000-10M/33FT-PC	10 m
P000001224	TT1000-12M/39FT-PC	12 m
P000001225	TT1000-30M/98FT-PC	30 m
P000001226	TT1000-45M/147FT-PC	45 m

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT