

XL-Trace Contractor Pack, Low Smoke Zero Halogen Self-Regulating Cable Kit



nVent RAYCHEM contractor packs comprise a fixed length of heating cable supplied in an easy-to-use and carry spool box. The spool allows the installer to feed out the required length easily, reducing installation time and effort.

CARATTERISTICHE

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Self-regulating technology: cut-to-length on site to mitigate any design variations

Quick and easy installation with the RayClic fast connection system

SPECIFICHE

Nominal Height:	6,8 mm
Nominal Width:	13,8 mm
Supply Voltage:	220 - 240 V
Temperatura minima di installazione:	-40 °C
Ground Path Type:	e collegamento
Outer Jacket Material:	Low Smoke Zero Halogen
Heating Cable Technology:	Self-Regulating

Table 1/1

Numero catalogo	Nome articolo	Lunghezza	Nominal Power Output @ 5°C, 230V	Max Continuous Exposure Temperature, Power On	Colore
1244-021262	XL-Trace-InstallerPack-10XL-30m	30 m	10 W/m	65 °C	Plum
1244-021263	XL-Trace-InstallerPack-10XL-50m	50 m	10 W/m	65 °C	Plum
1244-021264	XL-Trace-InstallerPack-10XL-80m	80 m	10 W/m	65 °C	Plum
1244-021265	XL-Trace-InstallerPack-15XL-50m	50 m	15 W/m	65 °C	Verde
1244-021266	XL-Trace-InstallerPack-15XL-80m	80 m	15 W/m	65 °C	Verde
1244-021267	XL-Trace-InstallerPack-26XL-50m	50 m	26 W/m	65 °C	Blu
1244-021268	XL-Trace-InstallerPack-26XL-80m	80 m	26 W/m	65 °C	Blu
1244-021269	XL-Trace-InstallerPack-31XL-50m	50 m	31 W/m	85 °C	Viola
1244-021270	XL-Trace-InstallerPack-31XL-80m	80 m	31 W/m	85 °C	Viola

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.

America del Nord

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

America Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT