

VPX System, Rugged, 10 U, 10 Slot, Pluggable PSU

CODICE A CATALOGO

20836-780



Rugged VPX system for 10 VPX boards 6 U, 1", 160 mm and 10 Rear I/O boards. The power for the system is supplied by a pluggable VPX power supply. A fan control module monitors the fans, the temperature and voltage.

CARATTERISTICHE

System designed in accordance with: MIL-STD-810F, MIL-STD-167, MIL-STD-461, IP 20

For rugged applications with increased shock and vibration resistance

PSU, 1 pluggable power supply, 1000 W, 6 U, space for a second PSU

Backplane VPX 10 slot, 6 U, in accordance with VITA 65, Backplane Profile BKP6-CEN10-11.2.4.4

100 to 240 VAC input on the back, main switch on the front of the chassis

LED voltage and fan fail indicator on the front

6 U Front card cage and 6U Rear I/O card cage, with 10 Slot VPX backplane

Prepared for Telescopic slides

Optimal EMC protection through hinged front and rear panel with integrated Honeycomp filter

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sistema

Numero di scanalature: 10

Tipo: Robusto montaggio a rack da 19"

Tipo di backplane: VPX, VITA 65

Trasferimento dati: 10 GbE; PCIe Gen3

Potenza per slot: 50W

Tensione di ingresso CA: 100 – 240V

Direzione del flusso d'aria: Dal davanti sul retro

Altezza del rack: 10U

Tipo di alimentazione: (1) PSU collegabile

Alimentazione inclusa: Sì

I/O posteriore: Sì

È conforme a: ANSI/VITA 46,0-2019

Potenza: 1000W

Profondità: 490mm

Altezza: 443.7mm

Larghezza: 480mm

Quantità nella confezione: 1

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Modified systems available on request.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE