

CPCI Serial System With 19" PSU, Desktop, 4 U, 8 Slot, 44 HP

CODICE A CATALOGO

24579-634



CompactPCI Serial Desktop Chassis with vertical Card Cage nine 3 U Boards and one CompactPCI 3 U Pluggable Power Supply.

CERTIFICAZIONI



CARATTERISTICHE

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0

System with vertical card cage. Board format Front: 3 U, 160 mm deep, 9 slot

Backplane 9 slot, 3 U, CompactPCI Serial; Power backplane

Heat dissipation by two radial fans, airflow front to rear

19" PSU, 300 W, 3 U, 8 HP

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sistema

Numero di scanalature: 9

Tipo: Desktop

Tipo di backplane: 3 U CompactPCI seriale con Ethernet Star

Trasferimento dati: PCIe Gen3

Potenza per slot: 30W

Tensione di ingresso CA: 100 – 240V

Direzione del flusso d'aria: Dal davanti sul retro

Altezza del rack: 4U

Tipo di alimentazione: (1) PSU collegabile

Alimentazione inclusa: Sì

I/O posteriore: No

È conforme a: PICMG CPCI-S.0 R2.0

Profondità: 275mm

Altezza: 177mm

Quantità nella confezione: 1

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Modified systems available on request.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE