

DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



KENMERKEN

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFICATIES

Producttype: DIN-rails

Table 1/2

Catalogusnummer	Materiaal	Hoogte	Lengte	Afwerking	Hoeveelheid in verpakking	Diepte
20118-872	Staal	35mm	125mm	Verzinkt	4	15mm
20118-873	Staal	35mm	175mm	Verzinkt	4	15mm
20118-874	Staal	35mm	275mm	Verzinkt	4	15mm
20118-875	Staal	35mm	375mm	Verzinkt	4	15mm
20118-876	Staal	35mm	475mm	Verzinkt	4	15mm

Catalogusnummer	Materiaal	Hoogte	Lengte	Afwerking	Hoeveelheid in verpakking	Diepte
20118-877	Staal	35mm	575mm	Verzinkt	4	15mm
20118-878	Staal	35mm	125mm	Verzinkt	4	7.5mm
20118-879	Staal	35mm	175mm	Verzinkt	4	7.5mm
20118-880	Staal	35mm	275mm	Verzinkt	4	7.5mm
20118-881	Staal	35mm	375mm	Verzinkt	4	7.5mm
20118-882	Staal	35mm	475mm	Verzinkt	4	7.5mm
20118-883	Staal	35mm	575mm	Verzinkt	4	7.5mm
20118-890	Staal	35mm	125mm	Verzinkt	10	7.5mm
20118-891	Staal	35mm	175mm	Verzinkt	10	7.5mm
20118-892	Staal	35mm	275mm	Verzinkt	10	7.5mm
20118-893	Staal	35mm	375mm	Verzinkt	10	7.5mm
20118-894	Staal	35mm	475mm	Verzinkt	10	7.5mm
20118-895	Staal	35mm	575mm	Verzinkt	10	7.5mm
20118-884	Staal	35mm	125mm	Verzinkt	10	15mm
20118-885	Staal	35mm	175mm	Verzinkt	10	15mm
20118-886	Staal	35mm	275mm	Verzinkt	10	15mm
20118-887	Staal	35mm	375mm	Verzinkt	10	15mm
20118-888	Staal	35mm	475mm	Verzinkt	10	15mm

Catalogusnummer	Materiaal	Hoogte	Lengte	Afwerking	Hoeveelheid in verpakking	Diepte
20118-889	Staal	35mm	575mm	Verzinkt	10	15mm

Table 2/2

Catalogusnummer	Breedte
20118-872	125mm
20118-873	175mm
20118-874	275mm
20118-875	375mm
20118-876	475mm
20118-877	575mm
20118-878	125mm
20118-879	175mm
20118-880	275mm
20118-881	375mm
20118-882	475mm
20118-883	575mm
20118-890	125mm
20118-891	175mm
20118-892	275mm
20118-893	375mm

Catalogusnummer	Breedte
20118-894	475mm
20118-895	575mm
20118-884	125mm
20118-885	175mm
20118-886	275mm
20118-887	375mm
20118-888	475mm
20118-889	575mm

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE