

Telescopic Slides C-Profile for Cabinet

Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

CERTIFICERINGEN



KENMERKEN

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

SPECIFICATIES

Materiaal:	Aluminium
Afwerking:	Geanodiseerd
Type:	C-profiel
Producttype:	Telescopische schuif

Table 1/1

Catalogusnummer	Diepte	Hoeveelheid in verpakking
-----------------	--------	---------------------------

24562-473	1200mm	2
24562-446	250mm	2
24562-449	600mm	2
24562-451	800mm	2
24562-452	900mm	2
24562-460	500mm	2
24562-461	600mm	2
24562-464	600mm	2
24562-466	800mm	2
24562-467	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-474	800mm	2

AANVULLENDE PRODUCTGEGEVENS

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE