

## Draaibaar voetstuk, S2MRB



Suspend 281-Max Rotary Base allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 300 degrees. Includes safety stop and maintenance-free bearing.

### KENMERKEN

---

Set screws and gasket are included

Surface mounting fasteners are not provided

Assembled Suspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

## SPECIFICATIES

| Table 1/1       |        |         |        |           |              |          |
|-----------------|--------|---------|--------|-----------|--------------|----------|
| Catalogusnummer | Hoogte | Breedte | Diepte | Materiaal | Afwerking    | Kleur    |
| S2MRB           | 167mm  | 125mm   | 125mm  | Aluminium | Gepoedercoat | Gitzwart |

## WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**