

Zonex roestvrijstalen wandmontagekasten, EXE-WM



The stainless steel single-door wall mounted enclosure, range EXE, with ATEX and IECEx certifications, is available off the shelf in 16 different sizes that accommodate the majority of common applications. ZONEX enclosures deliver a robust solution for termination and junction enclosure applications in potentially hazardous locations, including petroleum and chemical processing, water treatment processing, pharmaceutical processing, and grain processing. ZONEX enclosures are designed and certified to meet ATEX Directive 2014/34/EU, as well as IECEx standards for increased safety in housing electrical components in Zone 1 and Zone 2 applications.

INDUSTRIENORMEN

cULus_UL Listed

ATEX

CE

DoC NEC Class 1 Div 2

IECEx

KENMERKEN

ATEX- and IECEx-certified enclosure

Certification of final assembly is easier if enclosures are certified

Time and cost savings in the end-use investigation process of the final assembly

Body: M10 brass internal/external bonding provision; 2.5 mm thick wall-mounting brackets welded on the rear; M5 threads for gland plate screws provide quick and easy installation

Approvals: ATEX Directive 2014/34/EU. ATEX: Sira 09ATEX3224U; 2813 Ex II 2 G D; Ex e IIC Gb; Ex tb IIIC Db IP 66; EN 60079-0; EN 60079-7; EN 60079-31. IECEx: IECEx SIR 09.0099U; Ex eb IIC Gb; Ex tb IIIC Db IP 66; IEC 60079-0; IEC 60079-7; IEC 60079-31

Mounting plate: Fixed onto M8 welded studs to the rear of the enclosure; holes to facilitate cable fixing are on the top and bottom

Lock: Type 316L stainless steel quarter-turn latch with double bit 3 mm insert

Door: Continuous seal polyurethane gasket, operating range -40 to +70 °C; door opening 210°; door is easily removed by pulling clip-style hinge pins; M6 inner grounding stud; optional silicone gasket with operating range -55 to +180 °C

Delivery: Enclosure with door, mounting plate, gland plate and mounting accessories

Cable access: Fabricated and formed M5 threads for gland plate screws provide quick and easy installation; flat gasket

SPECIFICATIES

Dikte (T): 2.5mm
Voltooien: Geborsteld 320
Materiaal: Roestvrij staal 316L

Table 1/1


Catalogusnummer	Hoogte (H)	Breedte (W)	Diepte (D)	Paneelgrootte	Max. Montagediepte	Kabelinvoer
EXE303015SS61 E	300mm	300mm	150mm	255 x 255mm	100mm	237 x 74 mm
EXE303021SS61 E	300mm	300mm	210mm	255 x 255mm	160mm	237 x 134 mm
EXE403015SS61 E	400mm	300mm	150mm	355 x 255mm	100mm	237 x 74 mm
EXE403021SS61 E	400mm	300mm	210mm	355 x 255mm	160mm	237 x 134 mm
EXE404015SS61 E	400mm	400mm	150mm	355 x 355mm	100mm	337 x 74 mm
EXE404021SS61 E	400mm	400mm	210mm	355 x 355mm	160mm	337 x 134 mm
EXE504015SS61 E	500mm	400mm	150mm	455 x 355mm	100mm	337 x 74 mm
EXE504021SS61 E	500mm	400mm	210mm	455 x 355mm	160mm	337 x 134 mm
EXE505021SS61 E	500mm	500mm	210mm	455 x 455mm	160mm	437 x 134 mm
EXE605021SS61 E	600mm	500mm	210mm	555 x 455mm	160mm	437 x 134 mm
EXE606021SS61 E	600mm	600mm	210mm	555 x 555mm	160mm	537 x 134 mm
EXE606030SS61 E	600mm	600mm	300mm	555 x 555mm	250mm	537 x 224 mm

Catalogusnummer	Hoogte (H)	Breedte (W)	Diepte (D)	Paneelgrootte	Max. Montagediepte	Kabelinvoer
EXE755021SS61 E	750mm	500mm	210mm	705 x 455mm	160mm	437 x 134 mm
EXE756021SS61 E	750mm	600mm	210mm	705 x 555mm	160mm	537 x 134 mm
EXE757530SS61 E	750mm	750mm	300mm	705 x 705mm	250mm	687 x 224 mm
EXE906021SS61 E	900mm	600mm	210mm	855 x 555mm	160mm	537 x 134 mm

AANVULLENDE PRODUCTGEGEVENS

Opmerking: de behuizing met horizontale montagebeugels kan worden besteld door SS61E te vervangen door SS61HE in het artikelnummer.

DIAGRAMMEN



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE